



LAMP. MULTI ANGLE LOCKING HINGE HG-MA95A






[Locus chart]



[HG-MA95A-L]



Easily adjusts the flap angle by toggling the lever.
Lock allows the hinge to be held in position from 0° to 180° in 10° increments.
The flap is temporarily unlocked while the lever is pushed.
The flap stays unlocked when the lever is lifted.
Both hinge types can be used together.

[Applications]

Medical equipment, analytical instruments, semiconductor equipment. [Remarks]


Be sure to read the "Cautions"

[Recommended screws]


M5 screw



[Two ways to unlock]




The flap is temporarily unlocked while the lever is pushed.




The flap stays unlocked when the lever is lifted.






Rotation Angle 188°







Part Name Finish/ Colour Material 1 Bracket Steel Nickel 2 Base Plastic Cover 3 PC Black 4 Pin ABS

PA

Light Gray

5 Lever

Left-handed shown. Right-handed is symmetrical.

3×¢6.2

RoHS	CAD	Item Code	Item Name	Position	Туре	Max Torque N.m / pc	Max Torque kgf.cm/pc	Weight (g)	Box (pc)	Carton (pc)
G	3D	170-043-818	HG-MA95A-R	Right-handed	With lever	45	459	351	5	20
G	3D	170-043-819	HG-MA95A-L	Left-handed				351	5	20
G	3D	170-043-822	HG-MA95AF-R	Right-handed	Without lever	-	_	351	5	20
G	3D	170-043-823	HG-MA95AF-L	Left-handed				351	5	20

Refer to 1 : No.280 P.15

